



# **ITCS-RS**

Reset Unit




# Description


- Water resistant (IP-56) illuminated push button for call reset (completely resets all audio and visual signalization in system)
- Used in combination with ITCS-C3 calling unit, in system for call from refrigerating room
- Can be used for common reset as a part of hospital calling system (in case when ITCS-C1 and/or ITCS-C2 calling units are used)
- Red bulb in push button lights when call is done, until call is reset
- Bulkhead mounting (flush on request)

Reset unit used in ITCS-A calling system.


# **Technical Dimensions**

page 1/3





ITCS-R1, ITCS-S, ITCS-RS ITCS-C1, ITCS-C2, ITCS-C3, ITCS-C4



All dimensions in mm

# Specifications

#### **MECHANICAL**

Dimensions (WxHxD)	80x125x58 mm
Weight	0.23 kg

# **Used With**



## ITCS-1A-24VDC

Single Call Control Unit, 24 VDC



## ITCS-2A-24VDC

Double Call Control Unit, 24 VDC



### ITCS-2A-230VAC

Double Call Control Unit, 230 VAC



## ITCS-1A-230VAC

Single Call Control Unit, 230 VAC



## ITCS-C3

Refrigerator Calling Unit



#### ITCS-C2

Hospital Calling Unit



#### ITCS-C1

Hospital Calling Unit

page 3/3